


**NO-HUB COMPACT FIXTURE SUPPORTS
 WITH VERTICAL OFFSET FITTINGS FOR SIPHON JET WATER CLOSETS**


WITH SANITARY SWEEP INLET ON VENT SIDE

SINGLE




**Fig. 0416RY
 Top View**

DOUBLE



**Fig. 0416DY
 Top View**



Front View

-  Fig. 0416LY . . . NO-HUB L.H. Long Barrel
-  Fig. 0416RY . . . NO-HUB R.H. Long Barrel
-  Fig. 0416DY . . . NO-HUB Double Long Barrel


- NOTE:** See reverse side for recommended setting of closet outlet connection and various modifications.
- NOTE:** When used with concealed flush valve locate face plate behind supply pipe.
- NOTE:** Base support must be securely anchored to floor with four 1/2" (13) bolts provided by contractor.
- NOTE:** Fittings shown are regularly furnished with (1) 2" (51) NO-HUB sanitary sweep inlet.
- NOTE:** Side inlet 1 1/2" (38) or 2" (51) N.P.T. or 2" (51) caulk (specify type and size) Min © dimension of 1 1/2" (38) available using short nipple less coupling.

The water closet gasket regularly furnished is made of molded neoprene and designed to fit water closet outlet dimensions and configurations shown in ANSI Standard A112.19.2M-1995, Figure 13B. If gasket is not found to be compatible to fixture due to nonconformance of said fixture to ANSI A112.19.2M, then fixture manufacturer shall be consulted for a suitable gasket recommendation. Jay R. Smith assumes no liability for connections to fixtures which do not conform to these standards.

**© DIMENSION - ADJUS-TO-WALL
 TYPE OUTLET CONNECTION**

The Smith Adjus-to-Wall outlet connection provides adjustment at the face of the wall at the time the fixture is set; thus, compensating for wall construction variations. The © dimension is measured from the front of the face plate to the finished wall. To properly determine the length of nipple required, deduct 1" (25) from the © dimension. The Adjus-to-Wall coupling will provide 1/2" (13) horizontal adjustment in either direction with the coupling extended 5/16" (8) past face of the finished wall.

© dimension = 4" (100) (regularly furnished) consisting of nipple and Adjus-to-Wall coupling permitting adjustment from 3" (76) min. to 4" (100) max.



NOTE: Dimensions shown in parentheses are in millimeters.

NIPPLE LENGTHS AVAILABLE

LENGTH	MIN	©	MAX
2 1/2 (64)	2 1/4 (57)	3 1/4 (83)	
*3 1/4 (83)	3 (76)	4 (100)	
*8 1/4 (210)	8 (205)	9 (230)	
10 (255)	9 3/4 (250)	10 3/4 (275)	
12 (305)	11 3/4 (300)	12 3/4 (325)	
15 (380)	14 3/4 (375)	15 3/4 (400)	
18 (455)	17 3/4 (450)	18 3/4 (475)	

NOTE: When nipple lengths between 3 1/4" (83) and 8 1/4" (210) are specified, the 8 1/4" (210) nipple will be supplied. Nipple must be cut to specified length by others.

*ABS (Regularly Furnished) other lengths PVC.

DRAWING NUMBER
S0416Y

SIZE
A

SCALE:
NONE

DATE:
12-6-71

APPROVED BY:
RP

CHECKED BY:
RP

DRAWN BY:
RK

0416Y

FIGURE NUMBER

WE CAN ASSUME NO RESPONSIBILITY FOR USE OF SUPERSEDED OR VOID DATA

DIMENSIONS ARE SUBJECT TO MANUFACTURERS TOLERANCE AND CHANGE WITHOUT NOTICE

REV.	DATE	DESCRIPTION	BY	CKD. BY
J	7-1-98	Submittal Update	ASL	BS
H	1-26-98	Chg'd Callout	EMB	BS
G	3-5-97	Added Millimeters	EMB	BS
F	5-18-94	Submittal Update	EMB	BS

WEIGHT POUNDS	VOLUME CUBIC FEET	FIGURE NUMBER
		0416Y